

# pneumatic terminal LT-2-PK-3-DA

Part number: 5866

FESTO



## Data sheet

| Feature                            | Value   |
|------------------------------------|---|
| Operating pressure                 | 0.1 ... 8 bar   |
| Operating medium                   | Compressed air in accordance with ISO8573-1:2010 [-::-]                     |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| PWIS conformity                    | VDMA24364-B1/B2-L   |
| Ambient temperature                | -10 ... 60 °C   |
| Product weight                     | 5.2 g   |
| Pneumatic connection               | Barbed fitting PK-3   |
| Materials note                     | Conforms to RoHS  |