


# selector switch HW-6-38

Part number: 7199

FESTO



## Data sheet

Feature	Value
Valve function	8/6 bistable
Standard nominal flow rate	180 l/min
Operating pressure	0 ... 8 bar
Type of piloting	direct
Total leakage	1 l/h
PWIS conformity	VDMA24364-B1/B2-L
Nominal tightening torque	1.7 Nm
Tolerance for nominal tightening torque	± 10 %
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5