


solenoid coil VACS-C-C1-5

Part number: 8025331

FESTO

Type C connection pattern, to EN 175 301, 12 V DC



Data sheet

Feature	Value
Assembly position	Any
Conforms to standard	IEC 61010-1
Duty cycle	100 %
Insulation class	H
Characteristic coil data	12 V DC: 2.6 W
Permissible voltage fluctuation	+/- 10 %
Authorisation	c UL us - Recognized (OL)
Restriction ambient and medium temperature	-10 - 50 °C
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-10 ... 50 °C
Protection class	IP65
Ambient temperature	-10 ... 60 °C
Product weight	36.1 g
Electrical connection	Plug pattern type C to EN 175301-803 to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper