

manifold block

VABM-B10-25E-G12-2-P3

Part number: 8026279

FESTO



Data sheet

| Feature | Value |
|---|-------------------------------|
| Grid dimension | 27.5 mm |
| Assembly position | Any |
| Max. number of valve positions | 2 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Product weight | 726 g |
| Mounting type | with through hole |
| Pilot air port 12 | G1/8 |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 3 | G1/2 |
| Materials note | Conforms to RoHS |
| Material manifold | Wrought Aluminium alloy |