


manifold sub-base VABV-S1-1SB-G38

Part number: 8029812

FESTO



Data sheet

Feature	Value
Width	44 mm
Exhaust-air function	Via throttle plate
Based on the standard	ISO 5599-1
Max. number of valve positions	1
Operating pressure MPa	0 ... 1 MPa
Operating pressure	0 ... 10 bar
Suitability for vacuum	Yes
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-20 ... 60 °C
Medium temperature	-10 ... 50 °C
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-10 ... 50 °C
Product weight	490 g
Pneumatic connection, port 2	G3/8
Pneumatic connection, port 4	G3/8
Materials note	Conforms to RoHS
Material of connecting plate	Aluminium die cast