


# solenoid coil

## VACF-B-C1-5

Part number: 8030810

FESTO

Type C connection pattern, to EN 175 301, 12 V DC



## Data sheet

Feature	Value
Assembly position	Any
Conforms to standard	IEC 61010-1
Duty cycle	100 %
Insulation class	H
Characteristic coil data	12 V DC: 3.4 W
Permissible voltage fluctuation	+/- 10 %
Authorisation	c UL us - Recognized (OL)
Restriction ambient and medium temperature	-20 - 50 °C
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-20 ... 50 °C
Protection class	IP65
Ambient temperature	-20 ... 60 °C
Product weight	52.4 g
Electrical connection	Plug pattern type C to EN 175301-803 to EN 175301-803
Mounting type	With knurled nut
Materials note	Conforms to RoHS
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper