

plastic tubing
PAN-R-28X2,5-SW
Part number: 8036208

FESTO



Data sheet

Feature	Value
Outside diameter	28 mm
Bending radius relevant for flow rate	350 mm
Inside diameter	23 mm
Operating pressure for entire temperature range	-0.095 ... 0.8 MPa
Operating pressure complete temperature range	-0.95 ... 8 bar
Operating pressure for entire temperature range	-13.775 ... 116 psi
Temperature-dependent operating pressure	-0.095 ... 1.4 MPa
Temperature dependent operating pressure	-0.95 ... 14 bar
Temperature-dependent operating pressure	-13.775 ... 203 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-30 ... 80 °C
Product weight according to length	0.207 kg/m
Pneumatic connection	For push-in connector outside diameter 28 mm
Colour	Black
Shore hardness	D 62 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-A