

Fixed restrictor VFFG-T-F6-11

Part number: 8047356

FESTO

This type is suitable for vacuum.



Data sheet

Feature	Value
Valve function	Throttle function
Mounting type	Tapped
Operating pressure MPa	-0.09 ... 1 MPa
Operating pressure	-0.9 ... 10 bar
Ambient temperature	-5 ... 60 °C
Authorisation	c UL us - Recognized (OL)
Size	For ø 5.8 mm
Nominal size	1.15 mm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Product weight	1.2 g
Materials note	Conforms to RoHS