

# parallel kit EAMM-U-86-S62-87A-102

Part number: 8059032

FESTO

Suitable for electric drives.



## Data sheet

| Feature                  | Value                 |
|--------------------------|-----------------------|
| Size                     | 86                    |
| Assembly position        | Any                   |
| Max. speed               | 5,000 1/min           |
| PWIS conformity          | VDMA24364-B2-L        |
| Storage temperature      | -25 ... 60 °C         |
| Relative air humidity    | 0 - 95 %              |
| Protection class         | IP40                  |
| Ambient temperature      | -10 ... 60 °C         |
| Mass moment of inertia   | 175 kgmm <sup>2</sup> |
| No-load driving torque   | 0.25 Nm               |
| Transferable torque      | 9.5 Nm                |
| Product weight           | 2,500 g               |
| Interface code, actuator | S62                   |
| Interface code, motor in | 87A                   |
| Materials note           | Conforms to RoHS      |