


axial kit EAMM-A-L27-50GA

Part number: 8063454

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	2 Nm
Product weight	249 g
Interface code, actuator	L27
Interface code, motor in	50GA
Materials note	Conforms to RoHS