

electronics module VMPA14-FB-EMS-8

Part number: 8066764

FESTO



Data sheet

| Feature | Value |
|--|--|
| Diagnosis | Undervoltage, valves |
| Max. number of valve positions | 4 |
| Max. number of solenoid coils | 8 |
| Intrinsic current consumption at load voltage | 3 mA |
| Intrinsic current consumption at operating voltage | 8 mA |
| Nominal breakaway current per solenoid coil | 58 mA up to 24 ms |
| Nominal current with current reduction | 9 mA after 24 ms |
| Corrosion resistance classification CRC | 1 - Low corrosion stress (when installed) |
| PWIS conformity | VDMA24364-B1/B2-L |
| Product weight | 30 g |
| Material housing | POM |
| Materials note | Conforms to RoHS |