

electronics module VMPA14-MPM-EMM-4

Part number: 8066768

FESTO



Data sheet

Feature	Value
Max. number of valve positions	4
Max. number of solenoid coils	4
Nominal breakaway current per solenoid coil	80 mA up to 25 ms
Nominal current with current reduction	25 mA after 25 ms
Corrosion resistance classification CRC	1 - Low corrosion stress (when installed)
PWIS conformity	VDMA24364-B1/B2-L
Product weight	30 g
Material housing	POM
Materials note	Conforms to RoHS