

# double nipple NPFC-D-G12-G34-M

Part number: 8069216

FESTO



## Data sheet

Feature	Value
Material threaded fitting	Nickel-plated brass
Container size	10
Operating pressure	-0.95 ... 50 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-::-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 150 °C
Product weight	58.7 g
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G3/4
Materials note	Conforms to RoHS