

# operator unit CDSB-A1

Part number: 8070984

★ Core product range

FESTO



## Data sheet

Feature	Value
Max. line length	3 m
User memory	3 GB
Display	TFT colour
Display property	Touchscreen
Display size	1.77"
Operating voltage range DC	4.5 ... 5.5 V
Display resolution	128x160 Pixel
Authorisation	RCM Mark
KC mark	KC-EMV
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 70 °C
Relative air humidity	non-condensing Max. 95% at 60°C
Protection class	IP20
Ambient temperature	0 ... 60 °C
Product weight	36.6 g
USB interface, connection technology	USB 2.0 type B mini
Materials note	Conforms to RoHS
Material housing	PA6 reinforced
Area of application	Only with CMMT, CPX-E-CEC
Dimensions W x L x H	50 mm x 45 mm x 19,6 mm