


cover kit VAVC-F12-SCC-13-TP

Part number: 8084035

FESTO



Data sheet

Feature	Value
Nominal diameter DN	13
PWIS conformity	VDMA24364 zone III
Medium	Vapour Mineral oil-based hydraulic oil Inert gases Mineral oil Water Filtered compressed air, degree of filtration 200 µm Neutral fluids
Note on the medium	Gaseous media are only permitted with inflow via valve seat.
Medium temperature	-30 ... 200 °C
Ambient temperature	0 ... 60 °C
Storage temperature	-10 ... 60 °C
Assembly position	Any
Product weight	358 g
Materials note	Conforms to RoHS
Material cover	High alloy steel, non-corrosive
Material spindle seal	PTFE
Material seat seal	PTFE, modified