

safety clip NPAP-QE-S-Q16-P10

Part number: 8113233

FESTO



Data sheet

Feature	Value
Container size	10
Assembly position	Any
Operating pressure for entire temperature range	-0.095 ... 0.8 MPa
Operating pressure complete temperature range	-0.95 ... 8 bar
Operating pressure for entire temperature range	-13.775 ... 116 psi
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Ambient temperature	-5 ... 60 °C
Product weight	0.39 g
Pneumatic connection	For tubing outside diameter 16 mm
Materials note	Conforms to RoHS