


solenoid coil

VACC-S13-11-K4-1-NE4A

Part number: 8114135

FESTO



Data sheet

Feature	Value
Type of actuation	electrical
Assembly position	Any
Switching position indicator	No
Duty cycle	100 %
Required current consumption	16 mA
Insulation class	H
Max. input power	1,2 W
Max. input voltage	32 V
Max. input current	0,2 A
Characteristic coil data	14 - 32 V DC: 0.22 - 1.1 W
effective capacity	negligibly small
effective inductivity	negligibly small
Permissible voltage fluctuation	-15 % / +10 %
Explosion protection certification outside the EU	EPL Db (CN) EPL Gb (CN)
Certificate issuing department	GYJ20.1094X
Explosion ignition protection type Gas	Ex ia IIC T5/T6 Gb
Explosion ignition protection type Dust	Ex iaD 21 T95/T80
Explosion-proof ambient temperature	T5,T95°C: -30°C ≤ Ta ≤ +65°C T6,T80°C: -30°C ≤ Ta ≤ +50°C
PWIS conformity	VDMA24364 zone III
Protection class	IP65
Product weight	330 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Materials note	Conforms to RoHS