


# pilot valve

## VOFX-LT-M32C-MY-G18-SG18-1B2

Part number: 8119587

FESTO



## Data sheet

Feature	Value
Valve function	3/2 closed, monostable
Type of actuation	electrical
Width	22 mm
Standard nominal flow rate	50 l/min
Operating pressure	-0.9 ... 8 bar
Design structure	Directly actuated poppet valve
Type of reset	mechanical spring
Protection class	IP65
Nominal size	1.3 mm
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Manual override	detenting
Type of piloting	direct
Pilot air supply	Internal
Flow direction	non reversible
Switching time off	46 ms
Switching time on	31 ms
Duty cycle	100 %
Characteristic coil data	24 V DC; 3 W
Permissible voltage fluctuation	+/- 10 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
Medium temperature	-10 ... 50 °C
Ambient temperature	-10 ... 50 °C
Product weight	160 g
Electrical connection	3-pin Plug pattern type B to EN 175301-803 Plug to EN 175301-803
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	M5
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	PA