


parallel kit EAMM-U-60-D32-60P-91

Part number: 8125069

FESTO



Data sheet

Feature	Value
Size	60
Assembly position	Any
Max. speed	6,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	26.7 kgmm ²
No-load driving torque	0.07 Nm
Transferable torque	3 Nm
Product weight	1,130 g
Interface code, actuator	D32B
Interface code, motor in	60P
Materials note	Conforms to RoHS