

coupling

EAMD-56-46-24-23X27-U

Part number: 8134726

FESTO



Data sheet

Feature	Value
Holder diameter 1	24 mm
Holder diameter 2	23 mm
Size	56
Nominal length	46 mm
Assembly position	Any
Max. speed	5,500 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	151 kgmm ²
Transferable torque	75 Nm
Product weight	409 g
Materials note	Conforms to RoHS