


# gear unit EMGA-40-P-G12-SST-42

Part number: 8141763

FESTO



## Data sheet

Feature	Value
Gear unit flange size	40 mm
Motor flange size	42 mm
Torsional backlash	0.31 deg
Type of gear unit	Planetary gear unit
Gear unit ratio	12:1
Max. input speed	18,000 1/min
Operating temperature of gear unit	-25 ... 90 °C
PWIS conformity	VDMA24364-B2-L
Protection class	IP54
Continuous output torque	20 Nm
Mass moment of inertia of gear unit	0.026 kgcm <sup>2</sup>
Max. output torque	32 Nm
Max. efficiency	96 %
Torsional resistance	1 Nm/arcmin
Product weight	450 g
Gear unit interface, output shaft	40G
Gear unit interface, drive shaft	42A
Materials note	Conforms to RoHS