

reducing nipple NPFC-RS-G12-G38-MF

Part number: 8142598

FESTO



Data sheet

| Feature | Value |
|---|---|
| Material threaded fitting | Nickel-plated brass |
| Container size | 10 |
| Operating pressure | -0.95 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [-::-] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -10 ... 60 °C |
| Nominal tightening torque, pneumatic connection 1 | 47.9 Nm |
| Tolerance for nominal tightening torque | ± 20 % |
| Product weight | 22.84 g |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 2 | G3/8 |
| Materials note | Conforms to RoHS |
| Material seals | PVC |