

# cable connector NETC-M20-PBU-T26-EX4-E

Part number: 8151587

FESTO



## Data sheet

Feature	Value
Ambient temperature	-40 ... 75 °C
Protection class	IP66 IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
ATEX category Gas	II 2G
ATEX category Dust	II 2D
Explosion ignition protection type Gas	Ex eb IIC Gb
Explosion ignition protection type Dust	Ex tb IIIC Db
Explosion-proof ambient temperature	-40°C ≤ Ta ≤ +75°C
Explosion protection certification outside the EU	EPL Db (IEC-EX) EPL Gb (IEC-EX)
CE mark (see declaration of conformity)	to EU directive explosion protection (ATEX) in accordance with EU RoHS directive
Size	M20x1,5
Cable diameter	4 ... 13 mm
Colour	blue/black
Information on materials, cable connector	PA
Material seals	EPDM
Product weight	13 g
Container size	1
PWIS conformity	VDMA24364 zone III
Materials note	Conforms to RoHS