

sealing ring OL-M7

Part number: 8153155

FESTO



Data sheet

Feature	Value
Based on the standard	ISO 16030
Operating pressure for entire temperature range	-0.095 ... 3 MPa
Operating pressure complete temperature range	-0.95 ... 30 bar
Operating pressure for entire temperature range	-13.775 ... 435 psi
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-40 ... 100 °C
Manual tightening at ambient temperature	Yes
Nominal tightening torque	3 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	0.1 g
Pneumatic connection	M7
Materials note	Conforms to RoHS
Material stops	Aluminium
Material seals	HNBR