

Exhaust protection VABD-D3-L-GN12

Part number: 8177961

FESTO



Data sheet

Feature	Value
Assembly position	Any
Operating pressure MPa	0 ... 1.2 MPa
Operating pressure	0 ... 12 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364 zone III
Protection class	IP54
Ambient temperature	-50 ... 60 °C
Product weight	14 g
Mounting type	Threaded with external (male) thread
Materials note	Conforms to RoHS
Material vent screw	HP PA 12