


adding counter PZA-E-C

Part number: 8606

FESTO



Data sheet

Feature	Value
Design structure	mechanical sequence counter with pneumatic drive
Type of reset	Pushbutton or pneumatic signal
Display	6-place
Release pressure, drive unit	< 0,15 bar
Release pressure, return	< 0,15 bar
Response pressure, drive unit	> 0,8 bar
Response pressure, return	2 bar
Operating pressure	2 ... 8 bar
Minimum reset pressure	2 bar
Minimum pulse length, drive unit	8 ms
Minimum pulse length, return	150 ms
Minimum pause period, drive unit	10 ms
Minimum pause period, return	50 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Product weight	70 g
Mounting type	Front panel installation
Pneumatic connection	M5
Material housing	PA