

double nipple E-G3/8-3/8NPT

Part number: 9632

FESTO

With 2 sealing rings.



Data sheet

Feature	Value
Nominal size	11.5 mm
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Max. tightening torque, pneumatic connection 1	25 Nm
Max. tightening torque, pneumatic connection 2	22 Nm
Nominal tightening torque	38.5 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	25.5 g
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	3/8 NPT
Materials note	Conforms to RoHS