



Solenoid valve

MVH-5-1/4-L-B-VI

Part number: 117427

FESTO

With solenoid coil and manual override, without socket.



Data sheet

Feature	Value
Valve function	5/2 single solenoid
Working pressure	3 ... 10 bar
Operating medium	filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated
Pilot air port 12	G1/4
Pneumatic connection, port 1	G1/4
Pneumatic connection, 11	G1/4
Materials note	Contains PWIS substances