



Silencer AMTE-M-LH-G12

Part number: 1205863

★ Core product range

FESTO

Suitable for reducing noise at the exhaust ports of pneumatic systems.



Data sheet

| Feature | Value |
|---|--|
| Assembly position | Any |
| Container size | 10 |
| Operating pressure MPa | 0 ... 1 MPa |
| Working pressure | 0 ... 10 bar |
| Flow rate to atmosphere | 10,500 l/min |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Sound pressure level | 88 dB(A) |
| Ambient temperature | -40 ... 80 °C |
| Product weight | 43 g |
| Pneumatic connection | G1/2 |
| Material of silencer insert | Bronze |
| Material of threaded plug | Brass |
| Materials note | Conforms to RoHS |