

Parallel kit EAMM-U-60-D32-55A-91

Part number: 1210126

FESTO

Suitable for electric drives.



Data sheet

| Feature | Value |
|--------------------------|------------------------|
| Size | 60 |
| Assembly position | Any |
| Gear unit ratio | 1:1 |
| Max. speed | 6,000 1/min |
| PWIS conformity | VDMA24364 zone III |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP40 |
| Ambient temperature | -10 ... 60 °C |
| Mass moment of inertia | 26.7 kgmm ² |
| No-load driving torque | 0.07 Nm |
| Transferable torque | 3 Nm |
| Product weight | 1,050 g |
| Interface code, actuator | D32B |
| Interface code, motor in | 55A |
| Materials note | Conforms to RoHS |