

Coupling EAMC-30-35-6-8

Part number: 123041

FESTO

For DGE.



Data sheet

Feature	Value
Holder diameter 1	6 mm
Holder diameter 2	8 mm
Size	30
Nominal length	35 mm
Assembly position	Any
Max. speed	8,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	6.1 kgmm ²
Transferable torque	7.5 Nm
Product weight	45 g
Materials note	Conforms to RoHS