

Plastic tubing PUN-CM-10-SW

Part number: 130817

FESTO

Standard O.D tubing, for QS plug connectors, polyurethane (not approved for use in the food industry). Antistatic.



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	60 mm
Inside diameter	7 mm
Min. bending radius	30 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 ... 1 MPa
Temperature dependent working pressure	-0.95 ... 10 bar
Temperature-dependent operating pressure	-13.775 ... 145 psi
Surface resistance	0.01 ... 10 MOhm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight according to length	0.05158 kg/m
Pneumatic connection	For push-in connector outside diameter 10 mm
Color	Black
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)