

Individual subbase NAS-1/4-NPT-1A

Part number: 13994

FESTO

Based on standard ISO 5599-1, connection at side.



Data sheet

| Feature | Value |
|------------------------------------|---|
| Length | 24 mm |
| Working pressure | 16 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -10 ... 60 °C |
| Ambient temperature | -10 ... 60 °C |
| Mounting method for subbase | with through hole |
| Pneumatic connection, port 1 | NPT1/4-18 |
| Pneumatic connection, port 2 | NPT1/4-18 |
| Pneumatic connection, port 4 | NPT1/4-18 |