

Coupling

EAMD-28-22-14-10X12

Part number: 1453861

FESTO

drive component, which transmits the rotary motion of a stepper or servo motor



Data sheet

Feature	Value
Holder diameter 1	14 mm
Holder diameter 2	10 mm
Size	28
Nominal length	22 mm
Assembly position	Any
Max. speed	8,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	3.5 kgmm ²
Transferable torque	9 Nm
Product weight	43 g
Materials note	Conforms to RoHS