

# Axial kit EAMM-A-D40-60H

Part number: 1454242

FESTO

Suitable for electric drives.



## Data sheet

| Feature                  | Value                |
|--------------------------|----------------------|
| Assembly position        | Any                  |
| PWIS conformity          | VDMA24364-B2-L       |
| Storage temperature      | -25 ... 60 °C        |
| Relative air humidity    | 0 - 95 %             |
| Protection class         | IP40                 |
| Ambient temperature      | -10 ... 60 °C        |
| Transferable torque      | 12.5 Nm              |
| Product weight           | 570 g                |
| Interface code, actuator | D40A<br>D40B<br>D40C |
| Interface code, motor in | 60H                  |
| Materials note           | Conforms to RoHS     |