

Quick push-pull connector FCN-3-PK-3

Part number: 14768

FESTO

For plastic tubing PAN, PUN, PL, PP, PU.



Data sheet

Feature	Value
Nominal size	2 mm
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	0 ... 60 °C
Pneumatic connection, port 1	For tubing outside diameter 4 mm
Materials note	Conforms to RoHS
Material housing	Zinc die-casting