

Timer PZVT-300-SEC

Part number: 150239

FESTO



Data sheet

Feature	Value
Design structure	mechanical sequence counter with pneumatic actuator
Switch-off pressure	≤ 0.1 bar
Working pressure	2 ... 6 bar
Switch-on pressure	≥ 1.6 bar
Standard nominal flow rate	50 l/min
Adjustable delay times	20 ... 300 s
Setting accuracy	± 6 s
Pause period for reset	≥ 200 ms
Repetition accuracy, time setting	± 3 s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP54 With protective cover and panel frame to IEC 60529
Ambient temperature	-10 ... 60 °C
Product weight	45 g
Mounting type	Front panel installation
Pneumatic connection	Female thread M5
Materials note	Conforms to RoHS
Material housing	ABS