



Silencer UC-QS-6H

Part number: 165007

FESTO

Made of plastic.



Data sheet

Feature	Value
Assembly position	Any
Container size	1
Operating pressure MPa	0 ... 1 MPa
Working pressure	0 ... 10 bar
Flow rate to atmosphere	800 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
PWIS conformity	VDMA24364-B1/B2-L
Sound pressure level	60 dB(A)
Ambient temperature	-10 ... 70 °C
Product weight	1.1 g
Pneumatic connection	QS-6
Material of silencer insert	PE
Material of threaded plug	PE
Materials note	Conforms to RoHS