


Multi-position kit DPNC-40

Part number: 174419

FESTO

For connecting two cylinders with identical piston diameters to form a multi-position cylinder



Data sheet

Feature	Value
Size	40
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 ... 150 °C
Product weight	408 g
Materials note	Conforms to RoHS
Material mounting	Steel
Material threaded pin	Steel Galvanized
Material nut	Steel Galvanized