

Swivel flange SUA-50-R3

Part number: 176888

FESTO

For cylinders ADVU, AEVU. Matching clevis foot mounts LBN, LN, or LSN.



Data sheet

Feature	Value
Size	50
Assembly position	Any
Variants	Excellent corrosion protection
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	283 g
Materials note	Conforms to RoHS
Material mounting	Wrought Aluminum alloy With protective coating
Material mounting pin	High alloy steel, non-corrosive
Material sleeve	Spring steel
Material bearing	Plastic
Material screws	High alloy steel, non-corrosive
Material lock	High alloy steel, non-corrosive
Material shaft	High alloy steel, non-corrosive