


# Foot mounting CRHNC-40

Part number: 176938

FESTO

Corrosion resistant.



## Data sheet

| Feature                                 | Value   |
|---|---|
| Size                                    | 40  |
| Conforms to standard                    | ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290) |
| Corrosion resistance classification CRC | 4 - Very high corrosion stress  |
| PWIS conformity                         | VDMA24364-B2-L  |
| RSBP classification to CD-0033          | F5a   |
| Ambient temperature                     | -40 ... 150 °C  |
| Product weight                          | 188 g   |
| Materials note                          | Conforms to RoHS  |
| Material mounting                       | High alloy steel, non-corrosive   |
| Material screws                         | High alloy steel, non-corrosive   |