


Suction cup holder ESH-HA-4-PK

Part number: 189200

FESTO

without height compensator, vacuum connection at top, compensator secured by two hexagonal nuts.



Data sheet

| Feature | Value |
|---|--|
| Volume | 0.668 cm ³ |
| Assembly position | Vertical |
| Design structure | Vacuum connection at top |
| Correlation to suction-cup holder | Size 4 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-A1-L |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 23 g |
| Mounting type | with lock nut |
| suction cup mounting | M6 |
| Vacuum connection | PK-4 |
| Materials note | Conforms to RoHS |
| Material seals | NBR Steel |
| Material bracket | Aluminum Nickel-plated brass POM Heat-treatment steel High alloy steel |