

# Spiral plastic tubing PUN-4X0,75-S-0,5-SW

Part number: 197602

FESTO

Highly flexible, hydrolysis resistant to a great extent



## Data sheet

| Feature                                | Value  |
|--|--|
| Working length                         | 0.5 m  |
| Outside diameter                       | 4 mm   |
| Block length                           | 0.184 m  |
| Inside diameter                        | 2.6 mm   |
| Coil diameter                          | 25 mm  |
| Number of windings                     | 20   |
| Temperature dependent working pressure | -0.95 ... 10 bar   |
| Authorization                          | TÜV  |
| Certificate issuing department         | B 013277 0506 00   |
| Operating medium                       | Compressed air in accordance with ISO8573-1:2010 [7:::]  |
| PWIS conformity                        | VDMA24364-B2-L   |
| Ambient temperature                    | -35 ... 60 °C  |
| Product weight                         | 13 g   |
| Pneumatic connection                   | For push-in connector outside diameter 4 mm<br>for barbed connector internal diameter 3 mm with nut<br>for barbed connector internal diameter 3 mm |
| Color                                  | Black  |
| Shore hardness                         | D 52 +/-3  |
| Material tubing                        | TPE-U(PU)  |