

DUO spiral plastic tubing PUN-6X1-S-6-DUO-BS

Part number: 197622

FESTO

Highly flexible, hydrolysis resistant to a great extent



Data sheet

Feature	Value
Working length	6 m
Outside diameter	6 mm
Block length	2.228 m
Inside diameter	4 mm
Coil diameter	46 mm
Number of windings	168
Temperature dependent working pressure	-0.95 ... 10 bar
Authorization	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight	700 g
Pneumatic connection	For push-in connector outside diameter 6 mm for barbed connector internal diameter 4 mm with nut for barbed connector internal diameter 4 mm
Color	blue/black
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)