


Semi-rotary actuator DRRD-8-180-FH-PA

Part number: 2223060

FESTO



Data sheet

Feature	Value
Size	8
Cushioning angle	38 deg
Setting range of swivel angle on both sides	+10 / -100 deg
Swivel angle	180 deg
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Rack and pinion
Position detection	For proximity sensor
Operating pressure MPa	0.3 ... 0.8 MPa
Working pressure	3 ... 8 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364 zone III
Ambient temperature	-10 ... 60 °C
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	0.2 Nm
Permissible mass moment of inertia	0.0015 kgm ²
Product weight	155 g
Mounting type	with through hole with internal (female) thread Optional
Pneumatic connection	M3
Materials note	Conforms to RoHS
Material of drive shaft	High alloy steel, non-corrosive
Material seals	NBR TPE-U(PU)
Material housing	Wrought Aluminum alloy Smooth anodized