

Clamping sleeve EAMH-86-19-C27.3-P

Part number: 2406019

FESTO



Data sheet

| Feature | Value |
|------------------------|-----------------------|
| Size | 86 |
| Assembly position | Any |
| Max. speed | 5,000 1/min |
| PWIS conformity | VDMA24364-B2-L |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -10 ... 60 °C |
| Mass moment of inertia | 7.1 kgmm ² |
| Product weight | 78 g |
| Materials note | Conforms to RoHS |