


Clamping sleeve EAMH-110-25-C34

Part number: 2429561

FESTO



Data sheet

Feature	Value
Size	110
Assembly position	Any
Max. speed	5,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	23.4 kgmm ²
Product weight	133 g
Materials note	Conforms to RoHS