


Parallel kit EAMM-U-70-D32-60P-96-S1

Part number: 2619688

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Size	70
Assembly position	Any
Gear unit ratio	1:1
Max. speed	5,000 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP65
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	118 kgmm ²
No-load driving torque	0.18 Nm
Transferable torque	7 Nm
Product weight	1,770 g
Interface code, actuator	D32B
Interface code, motor in	60P
Materials note	Conforms to RoHS