

Sealing ring NPAS-C1-R-G38-P-FD-P10

Part number: 2652519

FESTO



Data sheet

Feature	Value
Container size	10
Assembly position	Any
Operating pressure for entire temperature range	-0.095 ... 1.2 MPa
Operating pressure complete temperature range	-0.95 ... 12 bar
Operating pressure for entire temperature range	-13.775 ... 174 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-:] Water (liquid, free of ice) Water vapour
Note on operating and pilot medium	Lubricated operation possible
PWIS conformity	VDMA24364-B2-L
Food-safe	See Supplementary material information
Ambient temperature	-20 ... 120 °C
Nominal tightening torque	35 Nm
Tolerance for nominal tightening torque	± 10 %
Product weight	0.15 g
Pneumatic connection	G3/8
Materials note	Conforms to RoHS
Material seals	PEEK