


Bellows cylinder EB-80-45

Part number: 2748904

FESTO

Maintenance-free, no stick/slip effect.



Data sheet

| Feature | Value |
|---|---|
| Size | 80 |
| Required installation diameter | 95 mm |
| Stroke | 45 mm |
| Max height when extended | 110 mm |
| Max. tipping angle | 15 deg |
| Max. offset | 10 mm |
| Min. installation height | 65 mm |
| Mode of operation | single-acting |
| Working pressure | 0 ... 8 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:::4] |
| Note on operating and pilot medium | Lubricated operation not possible |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -40 ... 70 °C |
| Reset force | 200 N |
| Product weight | 500 g |
| Mounting type | with internal (female) thread |
| Pneumatic connection | G1/4 |
| Materials note | Conforms to RoHS |
| Material bellows | CR |
| Material housing | Aluminum casting |